


The New Standard In Touch Point Disinfection.





Trusted by prestigious organisations to help control the spread of Coronavirus.

See STORM[®] in action - www.motorscrubberclean.com/fightingcoronavirus










STORM® and M-Wipes, the world's only spray applicator with wearable and disposable wipe system (Patent Pending) specifically invented for fast, targeted, disinfection of common touch points in the fight against Coronavirus.







Method For Flat Touch Point Disinfection.



We Made Disinfection Simple.

There are 2 important factors for effective disinfection.

- 1. A Perfect Liquid Layer of disinfectant must be created, with no gaps between the disinfectant droplets. See gaps, think risk!
- 2. The surface must stay wet for the contact time stated for your chosen chemical.

(Check your MSDS Sheet)




Gaps mean the surface is not fully covered with disinfectant, leaving the surface at risk of inhabiting viruses between the droplets and spreading infection.





Spray

Use STORM[®] 30cm(12in) away from the surface and spray from bottom to top, in a slow controlled motion.



Inspect

When the disinfectant is applied correctly, STORM[®] will achieve a Perfect Liquid Layer on flat surfaces. No wiping needed.




See gaps? Move closer to the surface and spray again in a slow, controlled motion with STORM[®].



Spray

Use STORM[®] 30cm(12in) away from the surface and spray from bottom to top, in a slow controlled motion.



Wipe

Dispense an M-Wipe from the on-board pouch and spray the wipe with STORM[®]. Now wipe the reverse side of the 3D touch point to apply disinfectant.

Never Use Paper Towels

Paper towels remove disinfectant from the surface, so the contact time is not achieved, rendering the whole process ineffective. "Studies suggest that Coronaviruses (including preliminary information on the COVID-19 virus) may persist on surfaces for a few hours or up to several days. This may vary under different conditions (e.g. type of surface, temperature or humidity of the environment)"

- WHO (World Health Organization) https://www.who.int/

Did You Know?

A lot of the equipment on the market are general sprayers, designed for many applications and are not specifically designed for virus disinfection.

The reverse side of door handles are high risk areas, due to general sprayers failing to give coverage on the reverse side.







Ergonomically Designed.

MotorScrubber battery backpack technology, guarantees all day comfort with padded back support and adjustable waist belt. No trailing cables mean the user is fully mobile, enabling the freedom to safely disinfect anywhere, whilst ensuring an effective disinfection experience.

- 3-4hr Usage (Ihr 50m Continuous)
- **On-board Solution** (Quick Reload)
- Lightweight & Fully Adjustable (Fits Any User)

ST·RN

HILLIAN AND THE HELLING

•O Multifunctional (Connect backpack to STORM™ and JET3)

Charge Time - 4-8hrs

LIGHTWEIGHT

Backpack secured to the waist maintaining perfect posture.



Kill Viruses On The Go.

STORM[®] delivers targeted, touch point disinfection, for proactive virus control. (STORM[®] can be used with any disinfectant)

Spray On Demand



- Ballistic, High Speed Swirl Nozzle (68 Micron)



Super Lightweight (0.3kg/0.66lb)



Soft Rubber Grip

Optimum Spray Distance - 30cm (12")

FATIGUE FREE USE

At just 0.3kg (0.66lb) the STORM® Wand is lightweight, designed for prolonged use and ensures the wrist is straight at all times.





2

1

Wipe Out The Risk.

The patent pending, M-Wipe System allows disinfectant to be applied to the reverse side of 3D touch points, which are often missed by other spraying machines. M-Wipes are a special non-absorbent, PP material, designed to apply disinfectant and not dry the surface, ensuring the specified contact/dwell time is achieved.

Fitting to the existing backpack system, the dispenser and disposal pouches allow for rapid wipe release and convenient wipe disposal.

M-WIPES FEATURES

- **On-board System** (Attaches To Existing Backpack)
- Heavy Duty & Durable Pouches
- (Quick Wipe Reload
- 🗐 Single Hand Dispensing



(1) WIPE DISPENSER POUCH

Dispense wipes with ease using our unique split funnel system. Holds one roll of 100 non-absorbent wipes.



WIPE DISPOSAL POUCH

(2)

Convenient wipe disposal. Pouch includes holster to store STORM® on the go.



M-Wipes Kit (MSS31) Includes one roll of M-Wipes, one wipe dispenser and one wipe disposal pouch.

Individual Item Price

M-Wipes 1 box = 6 rolls of 100 wipes - MSS30 Wipe Dispenser Pouch - MSJ62 Wipe Disposal Pouch - MSJ61

How To Use STORM[®] & M-Wipes

- Firstly spray the front of the 3D touch point with STORM®.
- Dispense one M-Wipe, then spray the wipe with disinfectant using STORM®.
- Wipe the reverse side of the 3D touch point ensuring full coverage.

This method vastly reduces the risk of cross infection.



One Backpack. Two Powerful Machines.

Military grade connectors make switching between STORM[®] and JET3 effortless. Simply click and go.



- (1) High Pressure Pump
- (2) Quick Change Solution Bottle
- (3) Battery Compartment
- (4) Coiled Cables For Manoeuvrability
- (5) Adjustable Belt (Fits any user)


- (6) Military Grade Connector Connects STORM[®]/JET3 to the battery.
- (7) Anti Drip Check Valve Connects STORM[®]/JET3 to the disinfectant.
- (8) Soft Rubber Grip
- (9) On Demand Button

a MotorScrubber JET/JET3 backpack.

JET3 Machine Only (MSJET3NOBACKPACK)

Spare batteries are available to increase machine runtime.

SJET3





Wall Dock mounts STORM[®], JET3 and BLADE to the wall for easy storage.

Take the weight off your back with the foldable bottle carrier. Featuring 8 slots for carrying 1 litre (0.25gl) refill bottles or rolls of M-Wipes.





The ultimate deep cleaning and virus control system Includes STORM®, JET3 and BLADE.

To find out more scan the QR code below.



10



Need more capacity?

LADE

BLADE is the ultimate mopping system. The 2 in 1 ultra-microfibre system delivers powerful cleaning performance.







